

X-431 O2-2 Scope Box Module overseas configuration Packing List

Date:2022/5/25

No.	Part category	Part name	Quantity
1	Main unit	O2-2 oscilloscope module,RoHS	1
2	Connector	HT201 attenuator (extended metal BNC connector)	2
3		USB data cable type a male to USB type B male, 1.2m, RoHS	1
4	Test cable	Double clamp power line (English), RoHS	1
5		HT25 secondary ignition pick-up line (long metal BNC connector, including plastic tail)	1
6		HT30 test line (long metal BNC connector, including plastic tail)	4
7		Needle Set (Colored 4mm Ffemale+20 needle+2 screw head)	1

No.	Part category	Part name	Quantity
8	Accessories	Crocodile clip, length 89.5,width 36,aperture 4.0,1000V,32A,black, TXGA,RoHS	2
9		Crocodile clip, length 89.5,width 36,aperture 4.0,1000V,32A,red, TXGA,RoHS	2
10		Multimeter probe, length 130.8, outer diameter 10.6, aperture 4.0,1000V,20A,black, TXGA,RoHS	2
11		Multimeter probe, length 130.8, outer diameter 10.6,aperture 4.0,1000V,20A,red, TXGA,RoHS	2
12		O2-2 oscilloscope Module Manual (English),RoHS	1
13		Clipper fuse 5*20mm	4

Packed by: yuanhe.wx

ADD: Launch Industrial Park, North of WuHe Road,BanXueGang Industrial Park, LongGang District, Shenzhen, Guangdong Province,P.R.China

Homepage: <http://www.cnlaunch.com> <http://www.x431.com>

TEL: 86-755-84528431 84528827; 86-755-84528888 (Telephone exchange); FAX: 86-755-84528454

Checked by: _____

